

Robots-Set ECBPi

ROB-SET ECBPi DOOSAN

Część nr.:10.03.01.00568

<https://www.schmalz.com/10.03.01.00568>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Generatory podciśnienia > Generator podciśnienia na końcu ramienia > Handling Sets ECBPi > ROB-SET ECBPi DOOSAN

Complete set for connecting and integrating the CobotPump ECBPi to lightweight robots




Construction use: CobotPump

for: Doosan Robotics

Type: M-,A-,H-Series

Dane projektowe



Atrybut	Wartość
H	188,80 mm
D	151,50 mm

Dane techniczne

Atrybut	Wartość
Suction rate (max.)	12 l/min
Rated power	13 W
Rated current	0,60 A
Operating temperature	5 ... 45 °C
for	Doosan Robotics
Product family	ROB-SET-ECBPI

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Robots-Set ECBPi

ROB-SET ECBPi DOOSAN

Część nr...:10.03.01.00568

<https://www.schmalz.com/10.03.01.00568>

Akcesoria



VEE 2xSPB1/SPF 154.3x42.3

Część nr...:10.01.36.00268

Number of cups: 2

Suct. cups: Suction cup SPB1/SPF

Length L: 154,3 mm

Width B: 42,3 mm



VEE 4xSPB1/SPF 218.3

Część nr...:10.01.36.00269

Number of cups: 4

Suct. cups: Suction cup SPB1/SPF

Length L: 218,3 mm



VEE SET-ECBPi

Część nr...:10.01.36.00266

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Robots-Set ECBPi

ROB-SET ECBPi DOOSAN

Część nr.:10.03.01.00568

<https://www.schmalz.com/10.03.01.00568>



RFBP 50 50 BA SPB2

Część nr.:10.01.45.00096

Length L: 50 mm

Width B: 50 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 100 58 BA SPB2

Część nr.:10.01.45.00091

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 100 58 BA O10

Część nr.:10.01.45.00092

Length L: 100 mm

Width B: 58 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm

Robots-Set ECBPi

ROB-SET ECBPi DOOSAN

Część nr.:10.03.01.00568

<https://www.schmalz.com/10.03.01.00568>



RFBP 120 120 BA SPB2

Część nr.:10.01.45.00085

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Suct. cups: Bellows suct. cup SPB2



RFBP 120 120 BA O10

Część nr.:10.01.45.00086

Length L: 120 mm

Width B: 120 mm

Connection: Bayonet connection

Material type: Foam O, Height 10 mm

Części zamienne



SPF 40 ED-65 G1/4-AG

Część nr.:10.01.01.13246

Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Robots-Set ECBPi

ROB-SET ECBPi DOOSAN

Część nr...:10.03.01.00568

<https://www.schmalz.com/10.03.01.00568>



SPB1 40 ED-65 G1/4-AG

Część nr...:10.01.06.03498

Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Number of folds: 1,5