

Vacuum pump

EVE-TR 10 AC3

Część nr.: 10.03.01.00137

<https://www.schmalz.com/10.03.01.00137>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Generatory podciśnienia > Pompy próżniowe > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 10 AC3

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: three-phase current

Sound level at 50 Hz: 60 dB(A)

Voltage at 50Hz: D175-260V/Y300-450V

Voltage at 60Hz: 200-300V o. 350-520V

Suction rate (50 Hz): 10 m³/h

Suction rate (60 Hz): 12 m³/h

Vacuum (50 Hz): -850 mbar


Rated power 50 Hz: 0,37 kW

Rated power 60 Hz: 0,45 kW

Permission: UL

Weight: 16 kg

Dane projektowe



Atrybut	Wartość
B	206 mm
B2	60 mm
d	7 mm
G3	G1/2-F
H	189 mm
L	429 mm
L2	106 mm
X1	160 mm
Y1	112 mm

Dane techniczne

Atrybut	Wartość
Suction rate (50 Hz)	10 m ³ /h
Suction rate (60 Hz)	12 m ³ /h
Voltage at 50Hz	D175-260V/Y300-450V
Voltage at 60Hz	
Rated power 50 Hz	0,37 kW
Rated power 60 Hz	0,45 kW

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Vacuum pump

EVE-TR 10 AC3

Część nr.:10.03.01.00137

<https://www.schmalz.com/10.03.01.00137>

Current type	AC3
Current type	three-phase current
Sound level at 50 Hz	60 dB(A)
Weight	16 kg
Protection type IP	IP 54
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Akcesoria



VBV -950...0 G1-AG EVE 10-40

Część nr.:10.03.01.00136

External diameter D: 46 mm

Max. vacuum: -950 mbar

Thread G1: G1"-M

Length L: 53,5 mm

Construction use: Pump EVE

Size: 10-40



MSS-K 1-1.6A

Część nr.:10.04.04.00118

Construction use: PKZM0

Protection type IP: IP 65


Measuring range: bar

Vacuum pump

EVE-TR 10 AC3

Część nr.:10.03.01.00137

<https://www.schmalz.com/10.03.01.00137>



VST EVE-TR-10

Część nr.:10.03.01.00132

Construction use: Pump EVE-TR

Size: 10

contains: Brush slide

and: Filter



VOL 15

Część nr.:10.03.03.00113

Reservoirs volume: 15 l

Height H: 180 mm

Add. function: Manometer, valve, filter

Części zamienne



FILT-EINS 3 65x70 PAP STF-3/4-IG

Część nr.:10.07.01.00017

Filter pore size: 3 µm

External diameter D: 65 mm

Length L: 69,5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 3/4-IG

Vacuum pump

EVE-TR 10 AC3

Część nr...:10.03.01.00137

<https://www.schmalz.com/10.03.01.00137>




FILT-EINS 39x40 EVE-10B+C-TR10

Część nr...:10.03.01.00021

Construction use: Pump EVE

Size: 10B+C-TR10



VST EVE-TR-10

Część nr...:10.03.01.00132

Construction use: Pump EVE-TR

Size: 10

contains: Brush slide

and: Filter