

Flat suction cup (round)

SGPN 20 SI-50 G1/8-AG

Część nr.: 10.01.01.11984

<https://www.schmalz.com/10.01.01.11984>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki do folii plastikowych i papieru > Flat Suction Cups SGPN > SGPN 20 SI-50 G1/8-AG

Przyssawka płaska (okrągła) do delikatnego chwytania papieru, folii, etc.



Size: 20

Suction cup material: Silicone SI


Material hardness [Shore A]: 50 Shore A

Nipple material: Aluminum

Material characteristics: FDA

Vacuum connection: G1/8"-M

Dane projektowe



Atrybut	Wartość
dn	3,50 mm
Dmax(S)	22 mm
Ds	20 mm
G1	G1/8"-M
H	16,40 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	8,50 N
Volume	0,60 cm ³
Hose diameter (rec.) d	2 mm
Size	20
Number of folds	0
Suction cup material	Silicone SI
Material hardness [Shore A]	50 Shore A

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SGPN 20 SI-50 G1/8-AG

Część nr.:10.01.01.11984

<https://www.schmalz.com/10.01.01.11984>

Weight	5,60 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N016 G1/8-AG DN350

Część nr.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SGP 20 SI-50 N016

Część nr.:10.01.01.11571

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 50 Shore A