

Flat suction cup (round)

SPF 40 ED-65 G1/4-AG

Część nr.: 10.01.01.13246

<https://www.schmalz.com/10.01.01.13246>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki do opakowań > Flat Suction Cups SPF > SPF 40 ED-65 G1/4-AG

Flat suction cup (round) for very dynamic handling of smooth and oily workpieces




Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Dane projektowe



Atrybut	Wartość
dn	6,10 mm
Dmax(S)	43,70 mm
Ds	41,40 mm
G1	G1/4"-M
H	22,20 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	2,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	49,50 N
Pull-off force	62,50 N
Lateral force	25 N
Volume	5,09 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Size	40

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SPF 40 ED-65 G1/4-AG

Część nr.:10.01.01.13246

<https://www.schmalz.com/10.01.01.13246>

Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	18,80 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Akcesoria



SIEB 17.5x0.8 MS-A2 280 0.28/0.16

Część nr.:10.07.01.00308

External diameter D: 17,5 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SU 40

Część nr.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C

Flat suction cup (round)

SPF 40 ED-65 G1/4-AG

Część nr...:10.01.01.13246

<https://www.schmalz.com/10.01.01.13246>



SC-SW 60 6

Część nr...:10.05.04.00096

Spanner size SW1: 6 mm

Nominal size: 60



SC-SW 80 6

Część nr...:10.05.04.00097

Spanner size SW1: 6 mm

Nominal size: 80



SC-SW 100 6

Część nr...:10.05.04.00098

Spanner size SW1: 6 mm

Nominal size: 100

Flat suction cup (round)

SPF 40 ED-65 G1/4-AG

Część nr.:10.01.01.13246

<https://www.schmalz.com/10.01.01.13246>



SC-SW 120 6

Część nr.:10.05.04.00099

Spanner size SW1: 6 mm

Nominal size: 120



SC-SW 200 6

Część nr.:10.05.04.00100

Spanner size SW1: 6 mm

Nominal size: 200



SC-SW 240 6

Część nr.:10.05.04.00101

Spanner size SW1: 6 mm

Nominal size: 240

Części zamienne

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SPF 40 ED-65 G1/4-AG

Część nr.:10.01.01.13246

<https://www.schmalz.com/10.01.01.13246>



SC 050 G1/4-AG MOD

Część nr.:10.01.06.02487

Connection geometry: 050

Connection: G1/4"-M

Length L1: 26,5 mm

Fitting length: 7,2 mm

Nominal diameter dn: 6,1 mm



SPF 40 ED-65 SC050

Część nr.:10.01.01.12373

Size: 40

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 15 mm