

Bellows suction cups SI-HD (round)

FSG 18 SI-HD-65 M5-AG

Część nr.:10.01.06.04166

<https://www.schmalz.com/10.01.06.04166>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki mieszkowe (okrągłe) > Bellows Suction Cups FSG (2.5 Folds) > FSG 18 SI-HD-65 M5-AG

Bellows suction cup (round) for very uneven workpieces



Size: 18

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: M5-M

Number of folds: 2,5

Vacuum connection: M5-M

Dane projektowe



Atrybut	Wartość
d2	8 mm
dn	2,50 mm
Dmax(S)	19 mm
Ds	17,20 mm
G1	M5-M
H	27,60 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Size	18
Number of folds	2,50
Connection	M5-AG
Curve radius (min) (convex)	20 mm
Volume	1,35 cm ³

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cups SI-HD (round)

FSG 18 SI-HD-65 M5-AG

Część nr.:10.01.06.04166

<https://www.schmalz.com/10.01.06.04166>

Suction force (-600mbar)	3,02 N
Pull-off force	8,50 N
Hose diameter (rec.) d	2 mm
Weight	2,90 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N016 M5-AG DN250

Część nr.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum



FG 18 SI-HD-65 N016

Część nr.:10.01.06.04148

Size: 18

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A