

Bellows suction cup HT2 (round)

SAB 30 HT2-65 G3/8-IG

Część nr.: 10.01.06.02425

<https://www.schmalz.com/10.01.06.02425>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki mieszkowe (okrągłe) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 30 HT2-65 G3/8-IG

Bellows suction pad (round) for very dynamic handling



Size: 30

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G3/8-IG

Number of folds: 1,5

Dane projektowe



Atrybut	Wartość
dn	4 mm
D1	32 mm
Dmax(S)	34 mm
Ds	30,60 mm
G1	G3/8"-F
H	44 mm
LG1	9,50 mm
SW1	22 mm
Z (Stroke)	9 mm

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	22 N
Pull-off force	33 N
Lateral force	29 N
Volume	5,60 cm ³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	30
Connection	G3/8"-F

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cup HT2 (round)

SAB 30 HT2-65 G3/8-IG

Część nr.:10.01.06.02425

<https://www.schmalz.com/10.01.06.02425>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	48,50 g
Number of folds	1,50
Product family	SAB