

Bellows suction cups (round)

FSGA 43 NBR-55 G1/4-IG

Część nr...10.01.06.00065

<https://www.schmalz.com/10.01.06.00065>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki mieszkowe (okrągłe) > Przyssawki mieszkowe FSGA (1,5 fałdy) > FSGA 43 NBR-55 G1/4-IG

Przyssawka mieszkowa (okrągła)



Size: 43

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A


Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 1,5

Vacuum connection: G1/4"-F

Dane projektowe



Atrybut	Wartość
d2	21,90 mm
Dmax(S)	47,50 mm
dn	4,40 mm
Ds	38 mm
G1	G1/4"-F
H	42,60 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Size	43
Number of folds	1,50
Connection	G1/4-IG
Curve radius (min) (convex)	60 mm
Volume	11,45 cm ³

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bellows suction cups (round)

FSGA 43 NBR-55 G1/4-IG

Część nr.:10.01.06.00065

<https://www.schmalz.com/10.01.06.00065>

Suction force (-600mbar)	22,80 N
Pull-off force	64,50 N
Hose diameter (rec.) d	6 mm
Weight	19 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N018 G1/4-IG DN440

Część nr.:10.01.06.01066

Nipple family: N 018

Thread G1: G1/4"-F

Length L1: 28,8 mm

Fitting length: 15 mm

Nominal diameter dn: 4,4 mm

Spanner size SW2: 5 mm

Material: Aluminum



FGA 43 NBR-55 N018

Część nr.:10.01.06.00131

Size: 43

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 1,5