

Flat suction cup (round)

SUF 1.5 HT1-60 M3-AG

Część nr.: 10.01.01.14207

<https://www.schmalz.com/10.01.01.14207>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki płaskie (okrągłe)
> Flat Suction Cups SUF > SUF 1.5 HT1-60 M3-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 1,5

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Vacuum connection: M3-M

Dane projektowe



Atrybut	Wartość
Dmax(S)	1,70 mm
Ds	1,50 mm
dn	1 mm
G1	M3-M
H	4,60 mm
LG1	3 mm
SW1	5 mm
Z (Stroke)	0,10 mm

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	0,08 N
Pull-off force	0,08 N
Volume	0,00 cm ³
Curve radius (min) (convex)	2 mm
Hose diameter (rec.) d	2 mm
Size	1,50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SUF 1.5 HT1-60 M3-AG

Część nr.:10.01.01.14207

<https://www.schmalz.com/10.01.01.14207>

Weight	0,20 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SC 010 M3-AG

Część nr.:10.01.06.04249

Connection geometry: 010

Vacuum connection: M3-M

Fitting length: 2 mm

Nominal diameter dn: 1 mm



SUF 1.5 HT1-60 SC010

Część nr.:10.01.01.13981

Size: 1,5

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A