

Flat suction cup (round)

PFYN 5 HT1-60 M5-AG

Część nr.: 10.01.01.11130

<https://www.schmalz.com/10.01.01.11130>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki płaskie (okrągłe)
> Płaskie przyssawki PFYN > PFYN 5 HT1-60 M5-AG

Przyssawka płaska (okrągły)



Size: 5

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: M5-M

Dane projektowe



Atrybut	Wartość
dn	1,50 mm
Dmax(S)	5,50 mm
Ds	5 mm
G1	M5-M
H	11,50 mm
LG1	4,50 mm
SW1	8 mm
Z (Stroke)	0,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	0,75 N
Volume	0,01 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	2 mm
Size	5
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

PFYN 5 HT1-60 M5-AG

Część nr...:10.01.01.11130

<https://www.schmalz.com/10.01.01.11130>

Weight	1,10 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N004 M5-AG DN200

Część nr...:10.01.01.03526

Thread G1: M5-M
Length L1: 13,5 mm
Fitting length: 5 mm
Material: Aluminum



PFG 5 HT1-60 N004

Część nr...:10.01.01.11158

Size: 5
Suction cup material: High temperature material HT1
Material hardness [Shore A]: 60 Shore A
Material property: non-marking