

Flat suction cup (oval)

SGON 30x10 HT1-60 G1/8-IG

Część nr.: 10.01.05.00421

<https://www.schmalz.com/10.01.05.00421>

Strona główna > Technologia podciśnienia w automatyce > Komponenty podciśnieniowe > Przyssawki podciśnieniowe > Przyssawki płaskie (owalne)
> Flat Suction Cups SGON > SGON 30x10 HT1-60 G1/8-IG

Przyssawka płaska (owalny)



Dimensions (LxB): 30 x 10

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Nipple material: Aluminum

Connection: G1/8"-F

Dane projektowe



Atrybut	Wartość
Bmax(S)	11,50 mm
Bs	9,40 mm
dn	2,50 mm
G1	G1/8"-F
H	25 mm
LG1	9 mm
Lmax(S)	30,50 mm
Ls	29,40 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Dane techniczne

Atrybut	Wartość
Suction force (-600mbar)	12,20 N
Volume	0,52 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	30 x 10
Number of folds	0
Suction cup material	High temperature material HT1

Kontakt z firmą Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (oval)

SGON 30x10 HT1-60 G1/8-IG

Część nr...:10.01.05.00421

<https://www.schmalz.com/10.01.05.00421>

Material hardness [Shore A] 60 Shore A

Weight 7,50 g

Product family SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Części zamienne



SA-NIP N022 G1/8-IG DN350

Część nr...:10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 13 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



ZOKL 11-13

Część nr...:10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel

Flat suction cup (oval)

SGON 30x10 HT1-60 G1/8-IG

Część nr.:10.01.05.00421

<https://www.schmalz.com/10.01.05.00421>



SGO 30x10 HT1-60 N022

Część nr.:10.01.05.00438

Dimensions (LxB): 30 x 10

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



ZOKL 11-13

Część nr.:10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel