

Plug union, elbow

STV-W G1/4-AG 8

Part no.:10.08.02.00161

<https://www.schmalz.com/10.08.02.00161>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/4-AG 8

Push-in Fitting, swivelling elbow



Thread G1: G1/4"-M


Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm

Design Data



Attribute	Value
d	8 mm
G1	G1/4"-M
dn	6,50 mm
D1	14,60 mm
H	14,80 mm
H1	22,70 mm
L	24 mm
L1	33,20 mm
LG1	7,50 mm
SW1	17 mm
SW3	16 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Nickel plated
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	49 g

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Plug union, elbow

STV-W G1/4-AG 8


Part no.:10.08.02.00161

<https://www.schmalz.com/10.08.02.00161>

Product family

STV

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C