

Plug union, elbow

STV-W G1/4-AG 6

Part no.:10.08.02.00462

<https://www.schmalz.com/10.08.02.00462>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/4-AG 6

Push-in Fitting, swivelling elbow



Thread G1: G1/4"-M


Hose diameter: 6 mm

Material: Plastics

Operating temperature: 0 ... 60 °C

Length L: 19,5 mm

Design Data



Attribute	Value
d	6 mm
G1	G1/4"-M
dn	6 mm
D1	14 mm
H	10,70 mm
H1	17,10 mm
L	19,50 mm
L1	27,50 mm
LG1	6 mm
SW1	16 mm

Technical Data

Attribute	Value
Hose type	Hose D = 6 d = 4
Hose type	6-4
Material	Plastics
Pressure range (operating pressure)	-0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Weight	19,30 g
Product family	STV

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si



Plug union, elbow

STV-W G1/4-AG 6

Part no.:10.08.02.00462

<https://www.schmalz.com/10.08.02.00462>

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 |
info@schmalz.si