

Compact ejector

SEM-C 50 SDA NO AS

Part no.:10.02.02.02966

<https://www.schmalz.com/10.02.02.02966>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Generators > Compact Ejectors > Compact Ejectors SEM-C > SEM-C 50 SDA NO AS

Multi-stage ejector (controllable) with high suction capacity



Size: 50

Add. function: Axial silencer

Suction rate (max.): 554 l/min


Air consumption suction: 190 l/min

Max. vacuum: -850 mbar

Control valve: Normally open

construction shape compact ejectors: With blow-off system

Design Data



Attribute	Value
B	94,50 mm
B1	210 mm
d	5,50 mm
D1	50 mm
G1	G1/4"-F
G2	G3/4"-F
G3	G3/4"-F
H	80 mm
L	219,50 mm
L1	339,50 mm
L2	10,50 mm
X1	183 mm
Y1	55 mm

Technical Data

Attribute	Value
Suction rate (max.)	554 l/min
Degree of evacuation	86 %
Air consumption suction	190 l/min
Control valve	Normally open

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Compact ejector

SEM-C 50 SDA NO AS


Part no.:10.02.02.02966

<https://www.schmalz.com/10.02.02.02966>

Weight	1,92 kg
Operating temperature	0 ... 50 °C
Size	50
Product family	SEM-C

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



ASK B-Form-C 5000 K-3P

Part no.:21.04.06.00084

Electrical connection: Fem connect Form C

Cable length: 5.000 mm

Material hose: PVC cable

Spare parts



SD G3/4-AG 50x120 SEM

Part no.:10.02.01.00312

Thread G1: G3/4"-M

External diameter D: 50 mm

Length L: 120 mm

Construction use: Multi-stage ejectors