

Bellows suction cups (round)

FSG 14 NK-45 M5-AG

Part no.:10.01.06.00433

<https://www.schmalz.com/10.01.06.00433>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 14 NK-45 M5-AG

Bellows suction cup (round) for very uneven workpieces



Size: 14

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A


Nipple material: Aluminum

Connection: M5-M

Number of folds: 2,5

Vacuum connection: M5-M

Design Data



Attribute	Value
d2	5,40 mm
dn	2,50 mm
Dmax(S)	15,50 mm
Ds	14,50 mm
G1	M5-M
H	27,80 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	14
Number of folds	2,50
Connection	M5-AG
Curve radius (min) (convex)	15 mm
Volume	0,98 cm ³

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSG 14 NK-45 M5-AG

Part no.:10.01.06.00433

<https://www.schmalz.com/10.01.06.00433>

Suction force (-600mbar)	1,37 N
Pull-off force	5,70 N
Hose diameter (rec.) d	2 mm
Weight	2,60 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SPI 14 PEEK

Part no.:10.01.06.03282

Size: 14

Material: Polyetheretherketon

Spare parts



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSG 14 NK-45 M5-AG

Part no...:10.01.06.00433

<https://www.schmalz.com/10.01.06.00433>



FG 14 NK-45 N016

Part no...:10.01.06.00453

Size: 14

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 2,5