

Flat suction cup (round)

SHFN 85 NK-45 G1/4-IG E MOS

Part no.:10.01.01.12213

<https://www.schmalz.com/10.01.01.12213>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups
SHFN > SHFN 85 NK-45 G1/4-IG E MOS

Flat suction cup (round) for highly dynamic handling of wood



Size: 85


Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Connection: G1/4-IG

Type: E

Design Data



Attribute	Value
d2	50 mm
dn	4,40 mm
Dmax(S)	89 mm
Ds	85 mm
G1	G1/4"-F
H	37,40 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	85
Suction cup material	Natural Rubber NK
Suction force d2	175 N
Suction force (-600mbar)	300 N
Lateral force	210 N
Volume	25 cm ³
Curve radius (min) (convex)	176 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SHFN 85 NK-45 G1/4-IG E MOS

Part no.:10.01.01.12213

<https://www.schmalz.com/10.01.01.12213>

Hose diameter (rec.) d	6 mm
Number of folds	0
Weight	97,80 g
Product family	SHFN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SIEB 14.5x1 MS-A2 0.103/0.15

Part no.:10.05.03.00023

External diameter D: 14,5 mm

Length L: 1 mm

Material: Brass / Stainless steel

Spare parts



SA-NIP N009 G1/4-IG DN440

Part no.:10.01.01.12192

Thread G1: G1/4"-F

Fitting length: 19,3 mm

Material: Aluminum

Flat suction cup (round)

SHFN 85 NK-45 G1/4-IG E MOS

Part no.:10.01.01.12213

<https://www.schmalz.com/10.01.01.12213>



SHF 85 NK-45 M10x1.25-IG E MOS

Part no.:10.01.01.12223

Size: 85

Thread G1: M10x1.25-F

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Type: E



SHF 85 NK-45 M10x1.25-IG E MOS

Part no.:10.01.01.12223

Size: 85

Thread G1: M10x1.25-F

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Type: E