

Flat suction cup (round)

SUF 18 SI-CO-55 SC030

Part no.:10.01.01.14035

<https://www.schmalz.com/10.01.01.14035>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 18 SI-CO-55 SC030

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 18

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d1	7,30 mm
d	5,30 mm
Dk	11,50 mm
Dmax(S)	20,60 mm
Ds	18 mm
H	9,30 mm
H2	4,30 mm
H3	5,80 mm
Z (Stroke)	1,80 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	13 N
Pull-off force	13 N
Volume	0,37 cm ³
Curve radius (min) (convex)	20 mm
Size	18
Nipple family	SC030
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SUF 18 SI-CO-55 SC030

Part no.:10.01.01.14035

<https://www.schmalz.com/10.01.01.14035>

Weight	1,10 g
Product family	SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 030 G1/8-AG

Part no.:10.01.06.04288

Connection geometry: 030

Vacuum connection: G1/8"-M

Fitting length: 6 mm

Nominal diameter dn: 3,1 mm



SC 030 G1/8-IG

Part no.:10.01.06.04307

Connection geometry: 030

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 3,1 mm