

Flat suction cup (round)

SG 10 NBR-55 N025

Part no.:10.01.01.00194

<https://www.schmalz.com/10.01.01.00194>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SG 10 NBR-55 N025

Flat suction cup (round)




Size: 10

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 13,5 mm

Design Data



Attribute	Value
d	3 mm
Dk	5 mm
Dmax(S)	11 mm
Ds	10 mm
H	13,50 mm
H2	8 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	10
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	4 N
Material hardness [Shore A]	55 Shore A
Product family	SG

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SG 10 NBR-55 N025

Part no.:10.01.01.00194

<https://www.schmalz.com/10.01.01.00194>

Accessories



SA-NIP N025 M5-AG DN200

Part no.:10.01.01.00318

Thread G1: M5-M

Fitting length: 3 mm

Material: Aluminum