

Bell suction cup (round)

SAG 80 NBR-60 G3/8-IG

Part no.:10.01.01.12170

<https://www.schmalz.com/10.01.01.12170>

Home > Bell-Shaped Suction Cups SAG > SAG 80 NBR-60 G3/8-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 80


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G3/8-IG

Design Data



Attribute	Value
dn	6 mm
Dmax(S)	90,70 mm
Ds	83 mm
G1	G3/8"-F
H	35 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	12,80 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	217 N
Lateral force	284 N
Lateral force (oily surface)	167 N
Volume	44 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Size	80
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bell suction cup (round)

SAG 80 NBR-60 G3/8-IG

Part no.:10.01.01.12170

<https://www.schmalz.com/10.01.01.12170>

Number of folds	0
Weight	45,20 g
Product family	SAG
