

Bell suction cup (round)

SAXM 50 ED-85 G1/4-AG

Part no.:10.01.19.00053

<https://www.schmalz.com/10.01.19.00053>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAXM > SAXM 50 ED-85 G1/4-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 50


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

Design Data



Attribute	Value
dn	6,10 mm
Dmax(S)	58,40 mm
Ds	51,50 mm
G1	G1/4"-M
H	32,80 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	8,40 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	109 N
Lateral force	58 N
Lateral force (oily surface)	110 N
Volume	14,40 cm ³
Curve radius (min) (convex)	25 mm
Hose diameter (rec.) d	6 mm
Size	50

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bell suction cup (round)

SAXM 50 ED-85 G1/4-AG

Part no.:10.01.19.00053

<https://www.schmalz.com/10.01.19.00053>

Connection	G1/4"-M
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	27,80 g
Product family	SAXM

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC-A 055 G1/4-AG L

Part no.:10.01.06.02821

Connection geometry: 055

Thread G1: G1/4"-M

Fitting length: 7,2 mm

Shape: Self Locking



SAXM 50 ED-85 SC055

Part no.:10.01.19.00006

Size: 50

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bell suction cup (round)

SAXM 50 ED-85 G1/4-AG

Part no...:10.01.19.00053

<https://www.schmalz.com/10.01.19.00053>



SC-S 055 FDC-L

Part no...:10.01.06.02804

Shape: Frict elem with Self lock