

Flat suction cup (round)

SAF 40 HT2-65 G3/8-IG

Part no.:10.01.01.12354

<https://www.schmalz.com/10.01.01.12354>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Flat Suction Cups SAF HT2 > SAF 40 HT2-65 G3/8-IG

Flat suction cup (round) for very dynamic handling



Size: 40

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Temperature resistance: 200 °C

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
dn	4 mm
Ds	41 mm
Dmax(S)	46 mm
G1	G3/8"-F
H	38 mm
LG1	9 mm
SW1	22 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Number of folds	0
Size	40
Suction force (-600mbar)	69 N
Temperature resistance	200 °C
Product family	SAF

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SAF 40 HT2-65 G3/8-IG

Part no.:10.01.01.12354

<https://www.schmalz.com/10.01.01.12354>

Accessories



SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C