

Flat suction cup (round)

SGPN 20 SI-50 G1/8-IG

Part no.:10.01.01.11985

<https://www.schmalz.com/10.01.01.11985>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 20 SI-50 G1/8-IG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 20

Suction cup material: Silicone SI


Material hardness [Shore A]: 50 Shore A

Nipple material: Aluminum

Material characteristics: FDA

Vacuum connection: G1/8"-F

Design Data



Attribute	Value
dn	3,50 mm
Dmax(S)	22 mm
Ds	20 mm
G1	G1/8"-F
H	22,40 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	8,50 N
Volume	0,60 cm ³
Hose diameter (rec.) d	2 mm
Size	20
Number of folds	0
Suction cup material	Silicone SI
Material hardness [Shore A]	50 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SGPN 20 SI-50 G1/8-IG

Part no.:10.01.01.11985

<https://www.schmalz.com/10.01.01.11985>

Weight	5,60 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 G1/8-IG DN350

Part no.:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SGP 20 SI-50 N016

Part no.:10.01.01.11571

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 50 Shore A