

Bellows suction cups (round)

SFB1 25 EPDM-45 G1/8-IG

Part no.:10.01.06.04413

<https://www.schmalz.com/10.01.06.04413>

Home > Vakuumska tehnologija za avtomatizacijo > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFB1 25 EPDM-45 G1/8-IG

Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 25

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Design Data



Attribute	Value
Dmax(S)	26,50 mm
Ds	25 mm
d2	8,20 mm
dn	4,10 mm
G1	G1/8-IG
LG1	8 mm
H	33,20 mm
SW1	14 mm
Z (Stroke)	6,50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	3,20 N
Volume	1,90 cm ³
Size	25
Number of folds	1,50
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Product family	SFB1

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

SFB1 25 EPDM-45 G1/8-IG

Part no.:10.01.06.04413

<https://www.schmalz.com/10.01.06.04413>

Spare parts



SFB1 25 EPDM-45 SC040

Part no.:10.01.06.04376

Size: 25

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 1,5



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm