

Schmalz Suction Plate Balance

SSPB-117 117-125 NBR

Part no...:10.01.15.00719

<https://www.schmalz.com/10.01.15.00719>

Home > Tehnologija stezanja vakuumu > Clamping Equipment for 3D Freeform Surfaces > Clamping Equipment for Manual Processing > Basic Holding Fixture BHF > SSPB-117 117-125 NBR

Suction plate with ball support for flexible clamping and gripping systems



Diameter Ds: 117 mm


Height H1: 137 mm

Stroke Z: 8 mm

Material: ED

Sealing material: Perbunan

Design Data



Attribute	Value
D	60 mm
Ds	117 mm
EH (max)	125 mm
EH (min)	117 mm
H1	137 mm
Z (Stroke)	8 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si