

Holder tooling suction Cup

HT-SG A5 I 10 46 RA AV VS

Part no.:10.07.06.00600

<https://www.schmalz.com/10.07.06.00600>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Mounting Elements > Holder System for Tooling HT > Holders for Suction Cups HT-SG I > HT-SG A5 I 10 46 RA AV VS

Holder for suction cup



Connection 1: Ball head 32 mm


Shape: integrated nozzle

Suction cup connection: Rectangular adapter

Connection: Rectangular adapter

Add. function: Atmospheric ventilation

Design Data



Attribute	Value
B	46 mm
B1	86,90 mm
B2	31 mm
B3	32 mm
D	32 mm
G4	G1/8"-F
H	24,50 mm
H1	47,70 mm
H2	4,80 mm
L	46,50 mm
L1	90,60 mm
L2	67 mm
L3	15 mm

Technical Data

Attribute	Value
Weight	256,80 g
Product family	HT-SG-I

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Holder tooling suction Cup

HT-SG A5 I 10 46 RA AV VS

Part no.:10.07.06.00600

<https://www.schmalz.com/10.07.06.00600>

Accessories



STV-GE G1/8-AG 6

Part no.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,4 mm

Length L: 16,4 mm



STV-W G1/8-AG 6

Part no.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20,8 mm