

Needle gripper

SNG-AP 10 1.2 V 10

Part no...:10.01.29.00381

<https://www.schmalz.com/10.01.29.00381>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Special Grippers > Needle Grippers > Needle Grippers SNG-AP > SNG-AP 10 1.2 V 10

Pneumatic needle gripper in maintenance-friendly design infinitely adjustable stroke




Number of needles: 10

Needle diameter: 1,2 mm

Needle stroke Z(NA): 10 mm

Pressure range (operating pressure): 3.0 ... 6.0 bar

Design Data



Attribute	Value
B	35 mm
G1	M5-F
G4	M5-F
H	105,50 mm
H2	64,40 mm
L	80 mm
L2	22 mm
W(E)	45 °
X1	29 mm
Y1	29 mm
Z(NA)	10 mm

Technical Data

Attribute	Value
Number of needles	10
Needle diameter	1,20 mm
Pressure range (operating pressure)	3.0 ... 6.0 bar
Operating temperature	5 ... 75 °C
Installation position	BEL
Weight	225 g

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Needle gripper

SNG-AP 10 1.2 V 10

Part no.:10.01.29.00381

<https://www.schmalz.com/10.01.29.00381>

Add. function

Product family

Variable stroke

SNG-AP

Accessories



BEF-PL 38x15x11.5 G1/4-IG SNG

Part no.:10.01.29.00403

Pressure range (operating pressure): bar

Length L: 38 mm

Width B: 15 mm

Height H: 11,5 mm

Thread G1: G1/4"-F

Construction use: Needle gripper



HTS-A2 SNG AP/AE OP

Part no.:10.01.29.00622

Pressure range (operating pressure): bar

Length L: 38 mm

Width B: 15 mm

Height H: 9,4 mm

Construction use: Needle gripper

Size: AP/AE



HTS-A3 SNG AP/AE OP

Part no.:10.01.29.00619

Pressure range (operating pressure): bar

Length L: 38 mm

Width B: 15 mm

Height H: 9,4 mm

Construction use: Needle gripper

Size: AP/AE

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Needle gripper

SNG-AP 10 1.2 V 10

Part no...:10.01.29.00381

<https://www.schmalz.com/10.01.29.00381>



HPS-SNG 2M6 AP/AE OP

Part no...:10.01.29.00666

Construction use: Needle gripper

Size: AP/AE

Shape: One-piece



SET SNG AP-Sensor

Part no...:10.01.29.00400

Construction use: Needle gripper

Size: AP-Sensor

contains: Sensor + mounting material



STV-W M5-AG 6

Part no...:10.08.02.00296

Pressure range (operating pressure): bar

Length L: 20,8 mm

Height H: 13 mm

Thread G1: M5-M

Needle gripper

SNG-AP 10 1.2 V 10

Part no.:10.01.29.00381

<https://www.schmalz.com/10.01.29.00381>



STV-GE M5-AG 6

Part no.:10.08.02.00201

Thread G1: M5-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 9,9 mm

Length L: 18,8 mm



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Spare parts



ERS SNG-AP/AE 10

Part no.:10.01.29.00420

Construction use: Needle gripper

Size: AP/AE


Needle stroke Z(NA): 10 mm

Needle gripper

SNG-AP 10 1.2 V 10

Part no...:10.01.29.00381

<https://www.schmalz.com/10.01.29.00381>



ERS SNG-AP/AE 10 1.2 10

Part no...:10.01.29.00408

Construction use: Needle gripper

Size: AP/AE

contains: 2 needle wedges mounted

Number of needles: 10

Needle diameter: 1,2 mm

Needle stroke Z(NA): 10 mm