

Compact ejector

SCP 15 FS

Part no.:10.02.02.00897

<https://www.schmalz.com/10.02.02.00897>

Home > Compact Ejectors SCP-FS > SCP 15 FS

Compact ejector with integrated functions



Nozzle diameter: 1,5 mm


Suction rate (max.): 65 l/min

Air consumption suction: 117 l/min

Pressure range (operating pressure): bar

Control valve: External control

Design Data



Attribute	Value
B	20,20 mm
d	4,50 mm
G1	G1/8"-F
G2	G1/8"-F
H	42,50 mm
H1	79 mm
H2	36,50 mm
H3	15 mm
L	71,50 mm
L2	7 mm
X1	41,50 mm
X2	58,50 mm
Y1	12 mm

Technical Data

Attribute	Value
Nozzle diameter	1,50 mm
Degree of evacuation	85 %
Suction rate (max.)	65 l/min
Control valve	External control
Suction rate (max.)	2,30 cfm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Compact ejector

SCP 15 FS

Part no.:10.02.02.00897

<https://www.schmalz.com/10.02.02.00897>

Product family

SCP

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Spare parts



FILT-EINS 13x33 PE-POR SCP

Part no.:10.02.02.00655

External diameter D: 12,5 mm

Length L: 33 mm

Filter material: Polyethylene

Construction use: Compact ejectors SCP



SD 28x19x31.5 SCP10/15

Part no.:10.02.02.00653

Length L: 28 mm

Width B: 19 mm

Height H: 31,5 mm

Construction use: Compact ejectors SCP