

Ejector module

SEP HV 2 04 7

Part no.:10.02.01.01393

<https://www.schmalz.com/10.02.01.01393>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Generators > Ejector Modules > Ejector Modules ecoPump SEP > SEP HV 2 04 7

Multistagenozzle as a cartridge



Shape: High Vacuum

Number of stages: 2

Nozzle size: 0,4 mm

Hole diameter: 7 mm

Degree of evacuation: 79 %


Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 13,2 l/min

Air consumption suction: 6,5 l/min

Design Data



Attribute	Value
D1	4,40 mm
D2	6,80 mm
L1	3,50 mm
L2	20,10 mm
L3	33 mm

Technical Data

Attribute	Value
Weight	0,80 g
Operating temperature	0 ... 60 °C
Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	4 mm
Pressure range (operating pressure)	2.0 ... 6.0 bar
Pressure range (operating pressure)	29.0 ... 87.0
Pressure optimal	4 bar
Pressure optimal	58 psi

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Ejector module

SEP HV 2 04 7

Part no.:10.02.01.01393

<https://www.schmalz.com/10.02.01.01393>

Sound level free	65 dB(A)
Sound level suction	57 dB(A)
Suction rate (max.)	0,81 m³/h
Suction rate (max.)	13,20 l/min
Suction rate (max.)	0,47 cfm
Air consumption suction	0,40 m³/h
Air consumption suction	6,50 l/min
Air consumption suction	0,23 cfm
Degree of evacuation	79 %
Number of stages	2
Nozzle size	0,40 mm
Hole diameter	7 mm
Shape	High Vacuum
Product family	SEP

Accessories



SHC 2 7

Part no.:10.02.01.01510

Number of stages: 2

Hole diameter: 7 mm

External diameter D: 6 mm

Length L: 6 mm

Thread G1: M8x0.5-M

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Ejector module

SEP HV 2 04 7

Part no...:10.02.01.01393

<https://www.schmalz.com/10.02.01.01393>



SFE 7 AL

Part no...:10.02.01.01464

Hole diameter: 7 mm

Width B: 19 mm

Height H: 22 mm

Length L: 37 mm

Thread G1: G1/8"-F

Thread G2: G1/8"-F

Compressed-air connection: G1/8"-F

Suction cup connection: G1/8"-F

Vacuum connection: G1/8"-F



SFE 7 POM

Part no...:10.02.01.01808

Hole diameter: 7 mm

Width B: 19 mm

Height H: 25 mm

Length L: 36,5 mm

Thread G1: M8x0.5-F

Thread G2: G1/8"-F

Compressed-air connection: M8x0.5-F

Suction cup connection: G1/8"-F



BEF-WIN 30x40x25.5 4 SFE-7

Part no...:10.08.03.00313

Width B: 30 mm

Height H: 40 mm

Length L: 25,5 mm

Construction use: Schmalz Fixation Element

Size: 7

Spare parts

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Ejector module

SEP HV 2 04 7

Part no...:10.02.01.01393

<https://www.schmalz.com/10.02.01.01393>



ERS SEP-07 6xRUE-KLAP

Part no...:10.02.01.01448

Construction use: Ejector module

Size: 07

contains: 6x flap