

Bellows suction cup (round)

FGA 6 NK-45 N004

Part no.:10.01.06.02604

<https://www.schmalz.com/10.01.06.02604>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 6 NK-45 N004

Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 6

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Number of folds: 1,5

Design Data



Attribute	Value
d	3,70 mm
d1	5,80 mm
d2	3 mm
D1	7,50 mm
Dk	7,20 mm
Dmax(S)	8 mm
Ds	5,70 mm
H	9 mm
H2	2 mm
H3	3,20 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	1,50
Suction force (-600mbar)	0,40 N
Size	6
Suction cup material	Natural Rubber NK
Weight	0,20 g
Curve radius (min) (convex)	2 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si



Bellows suction cup (round)

FGA 6 NK-45 N004

Part no...:10.01.06.02604

<https://www.schmalz.com/10.01.06.02604>

Product family

FGA

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 |
info@schmalz.si