

Bellows suction cups (round)

FSG 88 SI-55 G1/4-IG

Part no.:10.01.06.00018

<https://www.schmalz.com/10.01.06.00018>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 88 SI-55 G1/4-IG

Bellows suction cup (round) for very uneven workpieces



Size: 88

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 2,5

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
d2	29,30 mm
dn	8,20 mm
Dmax(S)	95,50 mm
Ds	89 mm
G1	G1/4"-F
H	101,50 mm
LG1	12 mm
SW1	21 mm
Z (Stroke)	34 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	88
Number of folds	2,50
Connection	G1/4-IG
Curve radius (min) (convex)	100 mm
Volume	143,67 cm ³

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSG 88 SI-55 G1/4-IG

Part no.:10.01.06.00018

<https://www.schmalz.com/10.01.06.00018>

Suction force (-600mbar)	40,46 N
Pull-off force	286 N
Hose diameter (rec.) d	9 mm
Weight	180 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



DR 88/64x5 MOS SI-15

Part no.:10.01.06.02620

External diameter D: 88 mm

Internal diameter d: 64 mm

Height H: 5 mm

Material type: Foam rubber

Sealing material: Silicone SI

Material hardness [Shore A]: 15 Shore A



SU 70

Part no.:10.01.01.12838

Size: 70

Clamping range: 65.0 ... 80.0 mm

Temperature resistance: 80 °C

Spare parts

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cups (round)

FSG 88 SI-55 G1/4-IG

Part no.:10.01.06.00018

<https://www.schmalz.com/10.01.06.00018>



SA-NIP N019 G1/4-IG DN820

Part no.:10.01.06.01960

Nipple family: N 019

Thread G1: G1/4"-F

Length L1: 38 mm

Fitting length: 15 mm

Nominal diameter dn: 8,2 mm

Spanner size SW2: 8 mm

Material: Aluminum



FG 88 SI-55 N019

Part no.:10.01.06.00147

Size: 88

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 2,5