

Flat suction cup (oval)

SGON 45x15 NBR-55 G1/4-IG

Part no.:10.01.05.00097

<https://www.schmalz.com/10.01.05.00097>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON
> SGON 45x15 NBR-55 G1/4-IG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 45 x 15


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

Design Data



Attribute	Value
Bmax(S)	16,50 mm
Bs	14,40 mm
dn	3 mm
G1	G1/4"-F
H	36 mm
LG1	12 mm
Lmax(S)	46 mm
Ls	44,40 mm
SW1	17 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	28,20 N
Volume	2,31 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	45 x 15
Number of folds	0
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (oval)

SGON 45x15 NBR-55 G1/4-IG

Part no.:10.01.05.00097

<https://www.schmalz.com/10.01.05.00097>

Material hardness [Shore A] 55 Shore A

Weight 14,30 g

Product family SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N023 G1/4-IG DN350

Part no.:10.01.05.00121

Thread G1: G1/4"-F

Length L1: 25 mm

Fitting length: 15 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



ZOKL 15-18

Part no.:10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (oval)

SGON 45x15 NBR-55 G1/4-IG

Part no...:10.01.05.00097

<https://www.schmalz.com/10.01.05.00097>



SGO 45x15 NBR-55 N023

Part no...:10.01.05.00153

Dimensions (LxB): 45 x 15

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



ZOKL 15-18

Part no...:10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel