

Flat suction cup (round)

PFYN 35 NBR-55 G1/8-IG

Part no.: 10.01.01.00089

<https://www.schmalz.com/10.01.01.00089>

Home > Flat Suction Cups PFYN > PFYN 35 NBR-55 G1/8-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 35


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-F

Design Data



Attribute	Value
dn	3,50 mm
Dmax(S)	38 mm
Ds	35 mm
G1	G1/8"-F
H	30 mm
LG1	9 mm
SW1	14 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	44 N
Volume	2,70 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	35
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	11,90 g

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFYN 35 NBR-55 G1/8-IG

Part no...:10.01.01.00089

<https://www.schmalz.com/10.01.01.00089>

Product family

PFYN

Number of folds

0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 30

Part no...:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N007 G1/8-IG DN350

Part no...:10.01.01.03523

Nipple family: N 007

Thread G1: G1/8"-F

Length L1: 24,5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Spanner size SW2: 4 mm