

Flat suction cup (round)

PFYN 40 PU-55 G1/8-AG

Part no.:10.01.01.00174

<https://www.schmalz.com/10.01.01.00174>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN
> PFYN 40 PU-55 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 40

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2,40 mm
Dmax(S)	43 mm
Ds	40 mm
G1	G1/8"-M
H	19 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	3,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	57,70 N
Volume	3,80 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	40
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFYN 40 PU-55 G1/8-AG

Part no.:10.01.01.00174

<https://www.schmalz.com/10.01.01.00174>

Weight 12,20 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 40

Part no.:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N007 G1/8-AG DN240

Part no.:10.01.01.03531

Nipple family: N 007

Thread G1: G1/8"-M

Length L1: 21 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2,4 mm

Material: Aluminum


Spanner size SW2: 4 mm

Flat suction cup (round)

PFYN 40 PU-55 G1/8-AG

Part no...:10.01.01.00174

<https://www.schmalz.com/10.01.01.00174>



PFG 40 PU-55 N007

Part no...:10.01.01.00056

Size: 40

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A