

Flat suction cup (round)

PFYN 80 PU-55 G1/4-AG

Part no.:10.01.01.00177

<https://www.schmalz.com/10.01.01.00177>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN
> PFYN 80 PU-55 G1/4-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 80


Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/4"-M

Design Data



Attribute	Value
dn	5,50 mm
Dmax(S)	86 mm
Ds	80 mm
G1	G1/4"-M
H	25 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	260 N
Volume	25 cm ³
Curve radius (min) (convex)	150 mm
Hose diameter (rec.) d	6 mm
Size	80
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFYN 80 PU-55 G1/4-AG

Part no.:10.01.01.00177

<https://www.schmalz.com/10.01.01.00177>

Weight 62,50 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 80

Part no.:10.01.01.12839

Size: 80

Clamping range: 80.0 ... 100.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

Thread G1: G1/4"-M

Length L1: 25 mm

Material: Aluminum

Flat suction cup (round)

PFYN 80 PU-55 G1/4-AG

Part no...:10.01.01.00177

<https://www.schmalz.com/10.01.01.00177>



PFG 80 PU-55 N009 M10x1.25-IG

Part no...:10.01.01.00059

Size: 80

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A