

Flat suction cup (round)

PFYN 10 NBR-CO-55 G1/8-AG

Part no.:10.01.01.10383

<https://www.schmalz.com/10.01.01.10383>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN
> PFYN 10 NBR-CO-55 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 10


Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2 mm
Dmax(S)	11,50 mm
Ds	10 mm
G1	G1/8"-M
H	12,50 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	1,40 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	4 N
Volume	0,07 cm ³
Curve radius (min) (convex)	12,50 mm
Hose diameter (rec.) d	4 mm
Size	10
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFYN 10 NBR-CO-55 G1/8-AG

Part no.:10.01.01.10383

<https://www.schmalz.com/10.01.01.10383>

Weight 4,10 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N004 G1/8-AG DN200

Part no.:10.01.01.03528

Thread G1: G1/8"-M

Length L1: 17 mm

Fitting length: 5 mm

Material: Aluminum



PFG 10 NBR-CO-55 N004

Part no.:10.01.01.10066

Size: 10

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si