

Flat suction cup (round)

PFYN 15 HT1-60 G1/8-IG

Part no.:10.01.01.11149

<https://www.schmalz.com/10.01.01.11149>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 15 HT1-60 G1/8-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 15

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: G1/8"-F

Design Data



Attribute	Value
dn	2 mm
Dmax(S)	17,50 mm
Ds	15 mm
G1	G1/8"-F
H	24 mm
LG1	9 mm
SW1	14 mm
Z (Stroke)	1,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Volume	0,40 cm ³
Curve radius (min) (convex)	12,50 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

PFYN 15 HT1-60 G1/8-IG

Part no.:10.01.01.11149

<https://www.schmalz.com/10.01.01.11149>

Weight 5,80 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N005 G1/8-IG DN200

Part no.:10.01.01.03521

Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20,5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum



PFG 15 HT1-60 N005

Part no.:10.01.01.11162

Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking