

## Flat suction cup (round)

SHFN 85 NK-45 G1/4-AG E TV

Part no.:10.01.01.12224

<https://www.schmalz.com/10.01.01.12224>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SHFN > SHFN 85 NK-45 G1/4-AG E TV

### Flat suction cup (round) for highly dynamic handling of wood



Size: 85


Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Connection: G1/4-AG

Type: E

### Design Data



| Attribute  | Value    |
|------------|----------|
| dn         | 4,40 mm  |
| Dmax(S)    | 89 mm    |
| Ds         | 85 mm    |
| G1         | G1/4"-M  |
| H          | 33,40 mm |
| LG1        | 10 mm    |
| SW1        | 17 mm    |
| Z (Stroke) | 4 mm     |
| d2         | 62 mm    |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value              |
|-----------------------------|--------------------|
| Size                        | 85                 |
| Suction cup material        | Natural Rubber NK  |
| Suction force d2            | 175 N              |
| Suction force (-600mbar)    | 300 N              |
| Lateral force               | 210 N              |
| Volume                      | 25 cm <sup>3</sup> |
| Curve radius (min) (convex) | 176 mm             |

### Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | [info@schmalz.si](mailto:info@schmalz.si)

## Flat suction cup (round)

SHFN 85 NK-45 G1/4-AG E TV

Part no.:10.01.01.12224

<https://www.schmalz.com/10.01.01.12224>

|                        |      |
|------------------------|------|
| Hose diameter (rec.) d | 6 mm |
| Number of folds        | 0    |
| Weight                 | 99 g |
| Product family         | SHFN |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



**SIEB 14.5x1 MS-A2 0.103/0.15**

Part no.:10.05.03.00023

External diameter D: 14,5 mm

Length L: 1 mm

Material: Brass / Stainless steel

### Spare parts



**TVN G1/4-AG 9 N009**

Part no.:10.05.10.00065

Thread G1: G1/4"-M

Thread G2: M10x1.25-M

Spring stroke Z: 9 mm

Nipple: N 009

## Flat suction cup (round)

SHFN 85 NK-45 G1/4-AG E TV

Part no...:10.01.01.12224

<https://www.schmalz.com/10.01.01.12224>



**SHF 85 NK-45 M10x1.25-IG E**

Part no...:10.01.01.12209

Size: 85

Thread G1: M10x1.25-F

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 45 Shore A

Type: E