

Flat suction cup (round)

SUF 40 NBR-55 G1/8-AG

Part no.:10.01.01.14090

<https://www.schmalz.com/10.01.01.14090>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 40 NBR-55 G1/8-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
Dmax(S)	44 mm
Ds	40 mm
dn	4,10 mm
G1	G1/8"-M
H	23,20 mm
LG1	7,50 mm
SW1	17 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	61 N
Pull-off force	61 N
Volume	3,80 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	40
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SUF 40 NBR-55 G1/8-AG

Part no.:10.01.01.14090

<https://www.schmalz.com/10.01.01.14090>

Weight	17,10 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 050 G1/8-AG

Part no.:10.01.06.04250

Connection geometry: 050

Vacuum connection: G1/8"-M

Fitting length: 7,2 mm

Nominal diameter dn: 4,1 mm



SUF 40 NBR-55 SC050

Part no.:10.01.01.13951

Size: 40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A