

Bell suction cup (round)

SAX 60 ED-85 RA

Part no.:10.01.19.00175

<https://www.schmalz.com/10.01.19.00175>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAX > SAX 60 ED-85 RA

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 60


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: Rectangular adapter

Number of folds: 0

Design Data



Attribute	Value
dn	6,75 mm
Dmax(S)	69,70 mm
Ds	61,50 mm
H	38,10 mm
L4	31,80 mm
SW1	22 mm
Z (Stroke)	10,90 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	154 N
Lateral force	107 N
Lateral force (oily surface)	155 N
Volume	25,20 cm ³
Curve radius (min) (convex)	30 mm
Size	60
Connection	Rectangular adapter
Number of folds	0

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bell suction cup (round)

SAX 60 ED-85 RA

Part no.:10.01.19.00175

<https://www.schmalz.com/10.01.19.00175>

Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	42,80 g
Product family	SAX