

Suction plate (round)

SPL-HT 90 ST G1/4-IG

Part no.: 10.01.23.00007

<https://www.schmalz.com/10.01.23.00007>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Suction Plates for High-Temperature SPL-HT > SPL-HT 90 ST G1/4-IG

Suction plate for high-temperature applications




Size: 90

Suction cup material: Silicate fabric ST

Connection: G1/4-IG

Working temperature max.: 600 °C

Design Data



Attribute	Value
dn	7 mm
Dmax(S)	111,50 mm
Ds	90 mm
G1	G1/4"-F
H	39 mm
LG1	12 mm
SW1	17 mm
SW2	8 mm
SW3	46 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	320 N
Volume	25 cm ³
Curve radius (min) (convex)	1060 mm
Evacuation rate for pu = -0,6 bar	32 l/min
Hose diameter (rec.) d	6 mm
Size	90
Working temperature max.	600 °C
Suction cup material	Silicate fabric ST

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Suction plate (round)


SPL-HT 90 ST G1/4-IG

Part no.:10.01.23.00007

<https://www.schmalz.com/10.01.23.00007>

Weight	675 g
Product family	SPL-HT

Spare parts




DR-SPL-HT 90 ST

Part no.:10.01.23.00016

Size: 90

Suction cup material: Silicate fabric ST



DR-SPL-HT 90 ST

Part no.:10.01.23.00016

Size: 90

Suction cup material: Silicate fabric ST