

Flat suction cup (round)

SGPN 40 HT1-60 G1/8-AG

Part no.:10.01.01.12847

<https://www.schmalz.com/10.01.01.12847>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 40 HT1-60 G1/8-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 40

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	5 mm
Dmax(S)	42 mm
Ds	40 mm
G1	G1/8"-M
H	25,60 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	2,30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	33 N
Volume	3,80 cm ³
Hose diameter (rec.) d	4 mm
Size	40
Number of folds	0
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Flat suction cup (round)

SGPN 40 HT1-60 G1/8-AG

Part no.:10.01.01.12847

<https://www.schmalz.com/10.01.01.12847>

Weight 11,10 g

Product family SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts




SA-NIP N035 G1/8-AG DN500

Part no.:10.01.01.11738

Thread G1: G1/8"-M

Fitting length: 5 mm

Material: Aluminum



SGP 40 HT1-60 N035

Part no.:10.01.01.12812

Size: 40

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A