

Bellows suction pad (round)

SFB1 15 SI-55 SC040

Part no...:10.01.06.04368

<https://www.schmalz.com/10.01.06.04368>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SFB1 15 SI-55 SC040

Bellows suction cup (round) with 1.5 corr. for dynamic handling workpieces




Size: 15

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1,5

Design Data



Attribute	Value
D1	11,50 mm
Dmax(S)	16 mm
Dk	12,80 mm
Ds	15 mm
d	7,50 mm
d1	10,40 mm
d2	4,70 mm
H	16 mm
H2	4,70 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	1 N
Volume	0,76 cm ³
Size	15
Number of folds	1,50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Curve radius (min) (convex)	12 mm
Nipple family	SC 040

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction pad (round)

SFB1 15 SI-55 SC040

Part no...:10.01.06.04368

<https://www.schmalz.com/10.01.06.04368>

Weight	1 g
Product family	SFB1

Accessories



SC 040 M5-AG

Part no...:10.01.06.04346

Connection geometry: 040

Vacuum connection: M5-M

Fitting length: 5 mm

Nominal diameter dn: 1,8 mm



SC 040 G1/8"-AG

Part no...:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20,2 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SC 040 G1/8"-IG

Part no...:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si



Bellows suction pad (round)

SFB1 15 SI-55 SC040

Part no...:10.01.06.04368

<https://www.schmalz.com/10.01.06.04368>

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 |
info@schmalz.si