

Bellows suction cup (round)

SPB1 25 ED-65 SC040

Part no...:10.01.06.02453

<https://www.schmalz.com/10.01.06.02453>

Home > Vakuum tehnologija za automatizaciju > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPB1 25 ED-65 SC040

Bellows suction cup (round) with 1.5 corr. for dynamic handling of cardboard and rigid packaging




Size: 25

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Number of folds: 1,5

Design Data



Attribute	Value
d	7,50 mm
d1	10,50 mm
d2	16,90 mm
D1	29 mm
Dk	15,10 mm
Dmax(S)	31,30 mm
Ds	26,40 mm
H	21 mm
H2	4,60 mm
Z (Stroke)	11 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	14,90 N
Pull-off force	23,40 N
Lateral force	13 N
Volume	5,25 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	25

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

SPB1 25 ED-65 SC040

Part no.:10.01.06.02453

<https://www.schmalz.com/10.01.06.02453>

Nipple family	SC 040
Number of folds	1,50
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	2,90 g
Product family	SPB1

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20,2 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

SPB1 25 ED-65 SC040

Part no...:10.01.06.02453

<https://www.schmalz.com/10.01.06.02453>



SIEB 11x1 MS-A2 280 0.28/0.16

Part no...:10.07.01.00309

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SPI 22 PA SPB1-25

Part no...:10.01.06.03315

Size: 22

Material: Polyamide

Use: SPB1-25



SC 040 NPT1/8-AG

Part no...:10.01.06.02541

Connection geometry: 040

Connection: NPT1/8-M

Length L1: 20,9 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bellows suction cup (round)

SPB1 25 ED-65 SC040

Part no...:10.01.06.02453

<https://www.schmalz.com/10.01.06.02453>



SC 040 NPT1/8-IG

Part no...:10.01.06.02542

Connection geometry: 040

Connection: NPT1/8-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm