Flat suction cup (round)

PFG 120 FPM-65 N010

Číslo dílu..:10.01.01.00389

https://www.schmalz.com/10.01.01.00389

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 120 FPM-65 N010

Flat suction cup (round) for smooth or slightly rough surfaces

- Size: 120
- Suction cup material: Fluorocaotchuc FPM
- Material hardness [Shore A]: 65 Shore A
- Material property: non-marking

Údaje o konstrukci



Atribut	Wert
d	7,30 mm
Dk	89,50 mm
Dmax(S)	124 mm
Ds	120 mm
H	23,50 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	540 N
Volume	75,16 cm³
Curve radius (min) (convex)	300 mm
Size	120
Nipple family	N 010
Suction cup material	Fluorocaotchuc FPM
Material hardness [Shore A]	65 Shore A

Flat suction cup (round)

PFG 120 FPM-65 N010

Číslo dílu..:10.01.01.00389

https://www.schmalz.com/10.01.01.00389

Weight	295,50 g
Product family	PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství

SA-NIP N010 G1/2-IG

Číslo dílu..:10.01.01.00796

- Thread G1: G1/2"-F
- Material: Aluminum

SU 120

Číslo dílu..:10.01.01.12437

- Size: 120
- Clamping range: 115.0 ... 130.0 mm
- Temperature resistance: 80 °C