Flat suction cup (round)

SG 25 NBR-55 N027

Part no..:10.01.01.00196

https://www.schmalz.com/10.01.01.00196


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SG 25 NBR-55 N027

Flat suction cup (round)



- Size: 25
- Suction cup material: Nitrile rubber NBR
- Material hardness [Shore A]: 55 Shore A
- Height H: 31 mm

Design Data



Attribute	Value
d	8 mm
Dk	12 mm
Dmax(S)	27 mm
Ds	25 mm
H	31 mm
H2	18 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	25
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	24 N
Material hardness [Shore A]	55 Shore A
Product family	SG

Contact Schmalz
Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au


Flat suction cup (round)

SG 25 NBR-55 N027

Part no..:10.01.01.00196

https://www.schmalz.com/10.01.01.00196

Accessories



SA-NIP N027 G1/8-AG DN350

Part no..:10.01.01.00320

Thread G1: G1/8"-M
Fitting length: 3 mm
Material: Aluminum