Flat suction cup (oval)

SGO 75x25 SI-HD-65 N023

Part no..:10.01.05.01040


https://www.schmalz.com/10.01.05.01040

Flat suction cup (oval) for narrow or curved workpieces



- Suction cup material: Silicone SI-HD
- Material hardness [Shore A]: 65 Shore A

Design Data



Attribute	Value
Bmax(S)	27.50 mm
Bs	24 mm
d	11.50 mm
d1	13 mm
dn	4 mm
Dk	17.50 mm
Lmax(S)	77 mm
Ls	74 mm
H	21 mm
H2	8 mm
H3	10 mm
Z (Stroke)	2.80 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	78.30 N
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	17.90 g
Product family	SGO

Contact Schmalz
Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Flat suction cup (oval)

SGO 75x25 SI-HD-65 N023

Part no..:10.01.05.01040

https://www.schmalz.com/10.01.05.01040


Accessories



SA-NIP N023 G1/4-AG DN350

Part no..:10.01.05.00122

Thread G1: G1/4"-M
Length L1: 25 mm
Fitting length: 5 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum



SA-NIP N023 G1/4-IG DN350

Part no..:10.01.05.00121

Thread G1: G1/4"-F
Length L1: 25 mm
Fitting length: 15 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum