Vacuum block

VCBL-R 160x96x45 40x40 TV

Part no..:10.01.12.02673

https://www.schmalz.com/10.01.12.02673


Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block VCBL-R > VCBL-R 160x96x45 40x40 TV

Vacuum block for grid tables



- Dimensions (LxB): 160 x 96
- Length L: 160 mm
- Width B: 80 mm
- Height H: 45 mm
- Grid: 40x40
- Recommended slot width x slot depth [mm]: 6,5x6,5 / 7,5x7,5 mm
- Add. function: Sensing valve

Design Data



Attribute	Value
B	80 mm
H	45 mm
H2	22 mm
L	160 mm
L1	160 mm

Technical Data

Attribute	Value
Grid	40x40
Weight	0.66 kg

Spare parts

Vacuum block

VCBL-R 160x96x45 40x40 TV

Part no..:10.01.12.02673

https://www.schmalz.com/10.01.12.02673



TV D9 4.3

Part no..:10.01.12.02514

External diameter D: 9 mm
Spring stroke Z: 4.3 mm
Length L: 22.8 mm



ERS VCBL-R Winkel

Part no..:10.01.12.02691

ERS VCBL-R


Part no..:10.01.12.02693

Vacuum block

VCBL-R 160x96x45 40x40 TV

Part no..:10.01.12.02673

https://www.schmalz.com/10.01.12.02673



DR 141/149x6 MOS NK-20

Part no..:10.01.12.02902

External diameter D: 141 mm
Internal diameter d: 149 mm
Length L: 6 mm
Width B: 4 mm
Height H: 6 mm
Material type: Foam rubber
Sealing material: Natural Rubber NK
Material hardness [Shore A]: 20 Shore A