Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD

Part no..:10.07.01.00266

https://www.schmalz.com/10.07.01.00266


Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF-D 60 P 4.5 F SSD

Dust filter (with pressure monitor)



- Connection: Ø60mm
- Shape: Piclon housing
- Nominal flow rate: 270 m³/h
- Filter pore size: 3 µm
- Add. function: Filter monitoring
- Additional function: Hose clamps SSD

Design Data



Attribute	Value
B1	221 mm
B2	112 mm
d	8.50 mm
D	170 mm
D1	198 mm
D2	60 mm
D3	60 mm
H	218 mm
L	355 mm
L1	658 mm
L2	303 mm
X1	192 mm

Technical Data

Attribute	Value
Connection	Ø60mm
Nominal flow rate	270 m³/h
Nominal flow rate	4500 l/min
Max. vacuum	-500 mbar
Filter pore size	3 µm
Weight	2.10 kg

Contact Schmalz
Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD

Part no..:10.07.01.00266

https://www.schmalz.com/10.07.01.00266

Product family	VF


Spare parts



FILT-EINS 3 124x320 PAP STF-Picl-4.5

Part no..:10.07.01.00060

Filter pore size: 3 µm
External diameter D: 124 mm
Length L: 320 mm
Filter material: Paper
Construction use: Dust filter STF
Size: Picl-4.5



DDW 10...50 250V-AC/6

Part no..:21.01.06.00011



SSD 60-68 ST-VZ

Part no..:10.07.10.00017

Clamping range: 60.0 ... 68.0 mm
Material: Steel
Surface: galvanised

Dust filter (with pressure monitor)

STF-D 60 P 4.5 F SSD

Part no..:10.07.01.00266

https://www.schmalz.com/10.07.01.00266



FILT-EINS 122x320 PAP STF-Picl-4.5

Part no..:11.04.03.10086

External diameter D: 122 mm
Length L: 320 mm
Filter material: Paper
Construction use: Dust filter STF
Size: Picl-4.5



FILT-EINS 3 124x320 PAP STF-Picl-4.5

Part no..:10.07.01.00060

Filter pore size: 3 µm
External diameter D: 124 mm
Length L: 320 mm
Filter material: Paper
Construction use: Dust filter STF
Size: Picl-4.5