Plug union, straight

STVI-GE G1/8-IG 4

Part no..:10.08.02.00149

https://www.schmalz.com/10.08.02.00149


Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STVI-GE G1/8-IG 4

Push-in Fitting, straight



- Thread G1: G1/8"-F
- Hose diameter: 4 mm
- Material: Brass
- Operating temperature: -20 ... 80 °C
- External diameter D: 8.5 mm
- Length L: 23.5 mm

Design Data



Attribute	Value
D	8.50 mm
d	4 mm
G1	G1/8"-F
L	23.50 mm
L2	9.50 mm
LG1	8 mm
SW1	14 mm

Technical Data

Attribute	Value
Hose type	Hose D = 4 d = 2
Hose type	4-2
Material	Brass
Pressure range (operating pressure)	1.00 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	16 g
Product family	STV

Plug union, straight

STVI-GE G1/8-IG 4

Part no..:10.08.02.00149

https://www.schmalz.com/10.08.02.00149

Accessories



VSL 4-2 PE BL

Part no..:10.07.09.00013

External diameter D: 4 mm
Internal diameter d: 2 mm
Length max.: 100 m
Material hose: PE
Pressure range (operating pressure): bar
Operating temperature: °C



VSL 4-2 PU MI-TR

Part no..:10.07.09.00001

External diameter D: 4 mm
Internal diameter d: 2 mm
Length max.: 50 m
Material hose: PU
Bending radius min.: 20 mm
Pressure range (operating pressure): -0.95 ... 10.00 bar
Operating temperature: -40 ... 60 °C



VSL 4-2.7 PA MI-TR

Part no..:10.07.09.00063

External diameter D: 4 mm
Internal diameter d: 2.7 mm
Length max.: 50 m
Material hose: PA
Bending radius min.: 30 mm
Pressure range (operating pressure): -0.95 ... 20.00 bar
Operating temperature: -40 ... 90 °C