Bellows suction cups (round)

FSG 12 NK-45 G1/8-AG

Part no..:10.01.06.00564

https://www.schmalz.com/10.01.06.00564


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 12 NK-45 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



- Size: 12
- Suction cup material: Natural Rubber NK
- Material hardness [Shore A]: 45 Shore A
- Nipple material: Aluminum
- Connection: G1/8"-M
- Number of folds: 2.5
- Vacuum connection: G1/8"-M

Design Data



Attribute	Value
d2	5 mm
dn	3.50 mm
Dmax(S)	13 mm
Ds	12 mm
G1	G1/8"-M
H	27 mm
LG1	7.50 mm
SW1	14 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	12
Number of folds	2.50
Connection	G1/8-AG
Curve radius (min) (convex)	12.50 mm
Volume	0.60 cm³

Bellows suction cups (round)

FSG 12 NK-45 G1/8-AG


Part no..:10.01.06.00564

https://www.schmalz.com/10.01.06.00564

Suction force (-600mbar)	1.18 N
Pull-off force	3.50 N
Hose diameter (rec.) d	4 mm
Weight	4.90 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories




SPI 14 PEEK

Part no..:10.01.06.03282

Size: 14
Material: Polyetheretherketon

Spare parts



SA-NIP N016 G1/8-AG DN350

Part no..:10.01.06.05735

Nipple family: N 016
Thread G1: G1/8"-M
Length L1: 20 mm
Fitting length: 6 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum

Bellows suction cups (round)

FSG 12 NK-45 G1/8-AG

Part no..:10.01.06.00564

https://www.schmalz.com/10.01.06.00564



FG 12 NK-45 N016

Part no..:10.01.06.00558

Size: 12
Suction cup material: Natural Rubber NK
Material hardness [Shore A]: 45 Shore A
Number of folds: 2.5