Mono-Base


ISMB-R 90x90x15 40x40

Part no..:10.01.15.00380

https://www.schmalz.com/10.01.15.00380


Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISMB-R 90x90x15 40x40

Mono-Base for grid tables



- Dimensions (LxB): 90x90
- Basic area: 90 x 90 mm
- Length L: 90 mm
- Width B: 90 mm
- Height H: 15 mm

Design Data



Attribute	Value
B	90 mm
d	60 mm
H	15 mm
L	90 mm

Technical Data

Attribute	Value
Weight	0.10 kg

Accessories

Mono-Base

ISMB-R 90x90x15 40x40

Part no..:10.01.15.00380

https://www.schmalz.com/10.01.15.00380



ISCUP Cup 1 80x80x30

Part no..:10.01.15.00003

Dimensions (LxB): 80 x 80
Length L: 80 mm
Width B: 80 mm
Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no..:10.01.15.00004

Dimensions (LxB): 80 x 40
Length L: 80 mm
Width B: 40 mm
Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no..:10.01.15.00005

Dimensions (LxB): 80 x 28
Length L: 80 mm
Width B: 28 mm
Height H: 30 mm